



selector valve

VHEF-EST-M32-M-G14

Part number: 4106807

★ Core product range

FESTO



Data sheet

| Feature | Value |
|---|---|
| Valve function | 3/2 open/closed, monostable |
| Type of actuation | manual |
| Width | 20 mm |
| Standard nominal flow rate | 870 l/min |
| Operating pressure MPa | -0.095 ... 1 MPa |
| Operating pressure | -0.95 ... 10 bar |
| Design structure | Poppet seat |
| Type of reset | mechanical spring |
| Nominal size | 6 mm |
| Exhaust-air function | throttleable |
| Instructions for use | Actuate only manually |
| Sealing principle | soft |
| Assembly position | Any |
| Type of piloting | direct |
| Flow direction | reversible |
| Overlap | Zero overlap |
| Max. switching frequency | 0.5 Hz |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Actuation torque | 0.4 Nm |
| Max. force on actuator | 200 N |
| Max. transverse force on actuator | 200 N |
| Product weight | 200 g |
| Mounting type | Front panel installation with through hole Optional |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Pneumatic connection, port 3 | G1/4 |
| Materials note | Conforms to RoHS |
| Material cover | PA-reinforced |
| Material seals | NBR |
| Material housing | Anodised wrought aluminium alloy |
| Material lever | PA-reinforced |