

Plastic tubing PP-4-NT

Part number: 4231

FESTO

For CK and CN connectors, suitable for higher pressures and temperatures, polyamide (not approved for use in the food industry).
Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	32 mm
Inside diameter	4 mm
Min. bending radius	14 mm
Temperature dependent operating pressure	-0.95 ... 19 bar
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-30 ... 80 °C
Authorisation	Germanischer Lloyd TÜV
Product weight according to length	0.0163 kg/m
Colour	neutral
Shore hardness	D 55 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-A