

quick T-connector TCK-3/8-PK-6

Part number: 4489

FESTO

Swivelling with 2 sealing rings.



Data sheet

Feature	Value
Nominal size	4.9 mm
Type of seal on screw-in stud	Sealing ring
Assembly position	Any
Design	T-shaped
Operating pressure for entire temperature range	-0.095 ... 1 MPa
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Nominal tightening torque	12.5 Nm
Tolerance for nominal tightening torque	± 20 %
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	For tubing outside diameter 8 mm for barbed connector internal diameter 6 mm with nut
Material of union nut	Anodised wrought aluminium alloy
Materials note	Conforms to RoHS
Material sealing ring	PA-reinforced TPE-U(PU)
Material housing	Zinc die-casting
Material hollow bolt	Anodised wrought aluminium alloy
Material swivel fitting	Zinc die-casting