

Drive shaft adapter DARF-Q11-16

Part number: 4835943

FESTO



Data sheet

Feature	Value
Size	16
For piston diameter	Ø16
Design	Drive shaft
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	60 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material screws	Nickel-plated steel