

Coupling EAMD-56-54-22-23X27

Part number: 5226828

FESTO



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Mounting diameter 1 | 22 mm |
| Mounting diameter 2 | 23 mm |
| Size | 56 |
| Nominal length | 54.5 mm |
| Mounting position | optional |
| Max. rotational speed | 5500 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C...60 °C |
| Mass moment of inertia | 172 kgmm ² |
| Transmittable torque | 60 Nm |
| Product weight | 457 g |
| Note on materials | RoHS-compliant |