

# Intermediate position attachment SLG-Z-8/12-A

Part number: 525680

FESTO



## Data sheet

Feature	Value
Mounting position	optional
Design	Stop as a rotary drive system in accordance with the gear rack and pinion principle
Position detection	Via proximity switch
Operating pressure	1 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Product weight	33.5 g
Type of mounting	Via through-hole and dowel pin
Pneumatic connection	M3
Material stops	Nickel-plated steel
Material seals	PUR
Material housing	Aluminium Hard anodised