

PAN-6x1-SI-P

Plastic tubing

Data sheet

Part no.: 526187

Page:1

Feature	Data/description
Nominal size of tubing	6
Internal diameter	4 mm
Outside diameter	6 mm
Bending radius min.	32 mm
Operating pressure min.	-0,95 bar
Operating pressure max. at 20°C	19 bar
Operating pressure max. at 30°C	16,5 bar
Operating pressure max. at 40°C	13,5 bar
Operating pressure max. at 50°C	12,5 bar
Operating pressure max. at 60°C	11 bar
Operating pressure max. at 70°C	10 bar
Operating pressure max. at 80°C	9 bar
Suitable for vacuum	Yes
Minimum ambient temperature	-30 °C
Maximum ambient temperature	80 °C
Material of tubing	TPE-A
Product weight per meter	0,0163 kg/m
Color	Silver