

PAN-10x1,5-SI-P

Plastic tubing

Data sheet

Part no.: 526189

Page:1

Feature	Data/description
Nominal size of tubing	10
Internal diameter	7 mm
Outside diameter	10 mm
Bending radius min.	58 mm
Operating pressure min.	-0,95 bar
Operating pressure max. at 20°C	17 bar
Operating pressure max. at 30°C	14,5 bar
Operating pressure max. at 40°C	12 bar
Operating pressure max. at 50°C	11 bar
Operating pressure max. at 60°C	10 bar
Operating pressure max. at 70°C	9 bar
Operating pressure max. at 80°C	8 bar
Suitable for vacuum	Yes
Minimum ambient temperature	-30 °C
Maximum ambient temperature	80 °C
Material of tubing	TPE-A
Product weight per meter	0,0417 kg/m
Color	Silver