


Plug SD-SUB-D-ST25

Part number: 527522

FESTO



Data sheet

Feature	Value
Type of mounting	With through-hole
Mounting position	optional
Product weight	51 g
Electrical connection	25-pin Plugs Sub-D
Operational voltage range DC	250 V
Operational voltage range AC	250 V
Permissible current load	5 A
Cable fitting	Pg11
Permissible cable diameter	7 mm...12 mm
Degree of protection	IP65
Ambient temperature	-20 °C...80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA
Material seals	NBR
Material electrical contact	Copper alloy Bronze