

Activated carbon filter MS4-LFX-1/4-R

Part number: 529467

FESTO



Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical +/-5°
Design	Activated carbon filter
Bowl guard	Plastic bowl guard
Operating pressure	0 bar...14 bar
Max. standard flow rate for clean air class	360 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [1:4:2] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air according to ISO 8573-1:2010 [1:4:1]
Media temperature	5 °C...30 °C
Residual oil content	0.003 mg/m ³
Ambient temperature	-10 °C...60 °C
Product weight	190 g
Type of mounting	Either: In-line installation With accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Note on materials	RoHS-compliant
Material filter	Activated carbon
Material housing	Die-cast aluminium
Material bowl	PC