

Quick coupling socket KD2-CK-4

Part number: 531622

FESTO



Data sheet

Feature	Value
Nominal size	2.9 mm
Operating pressure complete temperature range	-0.95 bar...12 bar
Standard nominal flow rate	123 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...80 °C
Product weight	16 g
Pneumatic connection, port 1	CK-4
Note on materials	RoHS-compliant