

# Lubricator MS6N-LOE-1/2-R-Z

Part number: 531714

FESTO

Plastic bowl with plastic bowl guard, direction of flow: from right to left.



## Data sheet

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	75 cm <sup>3</sup>
Bowl guard	Plastic guard
Inlet pressure 1	1 ... 16 bar
Minimum flow rate for lubricator function	50 l/min
Standard nominal flow rate	7,200 l/min
Operating medium	Filtered compressed air, 40 µm filtration
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	0 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 ... 60 °C
Product weight	600 g
Mounting type	with accessories Optional Line installation
Pneumatic connection, port 1	NPT1/2-14
Pneumatic connection, port 2	NPT1/2-14
Materials information, housing	Aluminium die cast
Materials information for bowl	PC