

Plug FBS-SUB-9-BU-2X5POL-B

Part number: 532219

FESTO



Data sheet

Feature	Value
Width	20 mm
Height	62 mm
Length	61 mm
Protocol	CAN
Product weight	60 g
Field bus interface	2x 5 spring-loaded terminals
Note on fieldbus interface	BUS In - BUS Out looped through
Permissible cable diameter	5 mm...10 mm
Degree of protection	IP65 IP67 In assembled state To IEC 60529
Ambient temperature	0 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material union nut	Brass
Material screws	Steel
Material seals	NBR