

MPA-MP-VI

Valve terminal

Feature	Data/description
Type of actuation	electrical
Flat silencer	at one end
Manual override	resetting detenting Covered
Valve terminal type	32
Design structure	Piston slide
Max. number of valve positions	24
Pilot air supply	external Internal
Valve function	3/2 5/2 5/3 2x2/2 2x3/2 monostable Bistable open closed pressurised exhausted open/closed
Valve terminal structure	modular and expandable
Switching position indicator	LED
Operating pressure	-0,9 - 10 bar
Pilot pressure	3 - 8 bar
Suitability for vacuum	Yes
Standard nominal flow rate	360 l/min
Nominal operating voltage DC	24 V
Corrosion resistance classification CRC	1

MPA-MP-VI**Valve terminal**

Feature	Data/description
Medium temperature	-5 - 50 °C
Protection class	IP65
Ambient temperature	-5 - 50 °C
Electrical actuation option	Multipol