

coupling

EAMC-42-50-14-20

Part number: 533710

FESTO



Data sheet

Feature	Value
Holder diameter 1	14 mm
Holder diameter 2	20 mm
Size	42
Assembly position	Any
Max. speed	6,000 1/min
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	138 g
Materials note	Conforms to RoHS