

# sub-base CDSV5.0-AS-1/8

Part number: 534434

FESTO

For CDSV individual valves, suitable for the food processing industry



## Data sheet

Feature	Value
Max. number of valve positions	1
Nominal operating voltage DC	24 V
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B2-L
Medium temperature	-5 ... 50 °C
Sound pressure level	75 dB(A)
Protection class	IP65 IP66 IP67 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	690 g
Electrical connection	Cable
Mounting type	with through hole with internal (female) thread
Scavenging orifice connection	M5
Pilot exhaust port 82/84	M5
Pilot air port 12	M5
Pilot air port 14	M5
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 4	G1/8
Pneumatic connection, port 5	G1/8
Materials note	Conforms to RoHS