

lubricator MS12N-LOE

Part number: 535044

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	12
Series	MS
Assembly position	Vertical +/- 5°
Operating pressure	1 ... 16 bar
Minimum flow rate for lubricator function	400 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:--:]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Storage temperature	-10 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 ... 60 °C
Mounting type	Line installation with accessories Optional
Material housing	Aluminium die cast
Material bowl	Wrought Aluminium alloy