


# Connecting cable NEBV-S1G25-K-5-N-LE25

Part number: 538226

FESTO



## Data sheet

Feature	Value
Type of mounting	4-40 UNC-2B
Product weight	910 g
Electrical connection 1	Sub-D socket, 25-pin
Electrical connection 2	Open end, 25-wire
Nominal operating voltage DC	24 V
Cable length	5 m
Cable characteristic	Standard
Min. cable bending radius	105 mm
Cable diameter	10.5 mm
Cable structure	20 x 0.25 mm <sup>2</sup> + 5 x 0.34 mm <sup>2</sup>
Degree of protection	IP65 IP67 In assembled state
Ambient temperature with moving cable	-5 °C...50 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
Material housing	PBT
Material union nut	PA
Material seals	TPE-O