

Fine filter MS4-LFM-1/8-BUV-Z

Part number: 539205

FESTO

1 µm filter, metal bowl guard, fully automatic condensate drain, flow direction from right to left.



Data sheet

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	1 µm
Filter efficiency	99.99 %
Condensate drain	fully automatic
Design structure	Fibre filter
Max. condensate volume	25 ml
Bowl guard	integrated as metal shell
Inlet pressure 1	2 ... 12 bar
Standard nominal flow rate	180 l/min
Operating medium	Filtered, unlubricated compressed air, 5 µm filtration
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Air purity class at output	2.7.3 per DIN ISO 8573-1
Medium temperature	5 ... 60 °C
Residual oil content	0.5 mg/m ³
Ambient temperature	5 ... 60 °C
Product weight	350 g
Mounting type	with accessories Optional Line installation
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Materials note	Free of copper and PTFE
Materials information for seals	NBR
Materials information for filter	Boron silicate fibre
Materials information, housing	Aluminium die cast
Materials information for bowl	Aluminium die cast Wrought Aluminium alloy
Materials info, viewing window	PA