

Plug socket MSSD-E-M12

Part number: 539711

FESTO



Data sheet

Feature	Value
Frequency of connection	50
Type of mounting	On solenoid valve via M3 central screw
Mounting position	optional
Product weight	11 g
Electrical connection 1	Angled socket, square design, 3-pin, type C
Electrical connection 2	Screw terminal
Operational voltage range DC	0 V...300 V
Operational voltage range AC	0 V...250 V
Current rating at 40° C	6 A
Cable fitting	M12
Permissible cable diameter	4 mm...6 mm
Connection cross section	0.75 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-20 °C...115 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	PA-reinforced
Housing colour	Black
Material seals	HNBR