

# Angled connection plate VABF-S4-1-A2G2-G14

Part number: 539721

FESTO



## Data sheet

| Feature                            | Value  |
|------------------------------------|--|
| Construction width                 | 26 mm  |
| Based on standard                  | ISO 15407-2  |
| Mounting position                  | optional   |
| Operating pressure                 | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar   |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 0 - No corrosion stress  |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L  |
| Degree of protection               | IP65<br>NEMA 4   |
| Ambient temperature                | -5 °C...50 °C  |
| Product weight                     | 217 g  |
| Type of mounting                   | With through-hole  |
| Material housing                   | Die-cast aluminium   |