

# quick coupling plug KS-3/8

Part number: 548138  
Product to be discontinued

FESTO

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



## Data sheet

Feature	Value
Nominal size	7.9 mm
Operating pressure	-0.95 ... 12 bar
Standard nominal flow rate	1,120 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Product weight	28 g
Pneumatic connection	G3/8