

spiral plastic tubing PAS-4I-6E-10

Part number: 548144
Product to be discontinued

FESTO

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|--|---|
| Working length | 10 m |
| Outside diameter | 6 mm |
| Block length | 0.56 m |
| Inside diameter | 4 mm |
| Coil diameter | 50 mm |
| Number of windings | 88 |
| Temperature dependent operating pressure | -0.95 ... 17.5 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7::-] |
| Ambient temperature | -30 ... 80 °C |
| Product weight | 250 g |
| Colour | blue |
| Shore hardness | D 55 +/-3 |
| Materials note | Free of copper and PTFE |
| Materials information for tubing | PA |