

spiral plastic tubing

PAS-6I-8E-10

Part number: 548146
Product to be discontinued

FESTO

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

Feature	Value
Working length	10 m
Outside diameter	8 mm
Block length	0.76 m
Inside diameter	6 mm
Coil diameter	50 mm
Number of windings	89
Temperature dependent operating pressure	-0.95 ... 17.5 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Ambient temperature	-30 ... 80 °C
Product weight	396 g
Colour	blue
Shore hardness	D 55 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	PA