

Multi-pin node VABE-S6-LT-C-S6-R5

Part number: 549046

FESTO



Data sheet

Feature	Value
Mounting position	optional
Max. number of valve positions	12 with monostable valves 6 with bistable valves
Max. resultant current	10 A
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C...50 °C
Product weight	760 g
Number of electrical connections	6
Electrical control	Multi-pin plug
Electrical connection	5-pin M12 Plugs
Material cover	PA
Material housing	Die-cast aluminium