

Plug socket with cable KMYZ-4-5,0-B-EX

Part number: 550482

FESTO



Data sheet

| Feature | Value |
|--|--|
| Maritime classification | See certificate |
| Type of mounting | On solenoid valve via M2 central screw |
| Mounting position | optional |
| Product weight | 62.5 g |
| Electrical connection | Angled socket Cable Square design MSZB |
| Operational voltage range DC | 3 V...36 V |
| Nominal operating voltage DC | 24 V |
| Current rating at 40° C | 1 A |
| Immunity to surge | 900 V |
| Protective conductor connection | Not available |
| Cable length | 5 m |
| Cable characteristic | Standard |
| Cable structure | 2 x 0.35 mm ² |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C...50 °C |
| CE mark (see declaration of conformity) | In accordance with EU RoHS Directive |
| CE marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| Material cable sheath | PVC |
| Material housing | PA |
| Material electrical contact | Bronze |