



# motor cable

## NEBM-S1G15-E-15-LE6

Part number: 550746  
 ☆ Core product range

Suitable for servo motor EMMS-ST-...

FESTO



## Data sheet

Feature	Value
Cable attribute	Suitable for chain link trunking
Operating voltage range DC	0 ... 72 V
Protection class	IP65
Note on degree of protection	in assembled condition
Ambient temperature with flexible cable installation	-5 ... 70 °C
Ambient temperature	-30 ... 70 °C
Bending radius, flexible cable installation	≥ 70 mm
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Angular
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	10
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	7
Electrical connection 2, occupied pins/wires	6
Wire ends	Wire end ferrule
Cable structure	7x0,5 Shielded
Cable diameter	8 mm
Cable length	15 m
Nominal conductor cross-section	0.5 mm <sup>2</sup>
Cable identification	Without inscription label holder
Cable sheath colour	Grey
Materials note	Conforms to RoHS
Materials information, cable sheaths	TPE-U(PUR)