

axial kit EAMM-A-F40-87A

Part number: 550936

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	21 Nm
Product weight	790 g
Interface code, actuator	F40
Interface code, motor in	87A
Materials note	Conforms to RoHS