

axial kit EAMM-A-F47-100A

Part number: 550949

FESTO

Suitable for electric drives.



Data sheet

| Feature | Value |
|--------------------------|------------------|
| Assembly position | Any |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Transferable torque | 21 Nm |
| Product weight | 1,010 g |
| Interface code, actuator | F47 |
| Interface code, motor in | 100A |
| Materials note | Conforms to RoHS |