

Plastic tubing PEN-10X1,5-RT

Part number: 551477

FESTO



Data sheet

| Feature | Value |
|--|--|
| Outside diameter | 10 mm |
| Flow-relevant bending radius | 40 mm |
| Inside diameter | 7 mm |
| Min. bending radius | 23.5 mm |
| Tubing characteristics | Suitable for energy chains |
| Temperature-dependent operating pressure | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Note on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Approval | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0506 00 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7::-:] Water (liquid, ice-free) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature | -30 °C...60 °C |
| Product weight according to length | 0.03766 kg/m |
| Pneumatic connection | For push-in connector O.D. 10 mm |
| Colour | Red |
| Shore hardness | D 52 +/-3 |
| Note on materials | RoHS-compliant |
| Material tubing | PE |