

Adapter lens SASF-L1-LS2-M4

Part number: 552831

FESTO



Data sheet

Feature	Value
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP66
Ambient temperature	-30 °C...150 °C
Tightening torque	-0.2 Nm...0.6 Nm
Product weight	0.7 g
Lens function	Focusing Light spot diameter 0.7 mm at a distance of 10 mm Depending on the light guide
Material housing	Aluminium Anodised