

micro filter

MS9-LFM-1-AUM-HF

Part number: 553038

FESTO

0.01 µm filter, metal bowl guard, high flow rate, manual condensate drain, flow direction from left to right.



Data sheet

Feature	Value
Series	MS
Size	9
Design structure	Fibre filter
Grade of filtration	0.01 µm
Condensate drain	manual rotary
Operating pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2]
Max. standard flow rate for air quality class	7,800 l/min
Min. standard flow rate for air quality class	390 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Storage temperature	-10 ... 60 °C
Residual oil content	0.01 mg/m ³
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Material housing	Aluminium die cast
Material of cover	PA
Material filter	Boron silicate fibre
Material bowl	Wrought Aluminium alloy
Material screen	PA
Material seals	NBR
Product weight	2,500 g