

Bellows kit DADB-V6-32-S126-175

Part number: 553275

FESTO



Data sheet

Feature	Value
Outside diameter	38 mm
Size	32
Stroke range	126 mm...175 mm
Piston rod extension	61 mm
Design	Round Bellows kit With ducted exhaust air
Mounting position	optional
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C...80 °C
Product weight	52 g
Type of mounting	Push-on Via threaded pin
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel