

# Bellows kit DADB-V6-40-S176-250

Part number: 553297

FESTO



## Data sheet

| Feature                        | Value   |
|--------------------------------|---|
| Outside diameter               | 46 mm   |
| Size                           | 40  |
| Stroke range                   | 176 mm...250 mm                                 |
| Piston rod extension           | 72 mm   |
| Design                         | Round<br>Bellows kit<br>With ducted exhaust air |
| Mounting position              | optional  |
| Corrosion resistance class CRC | 3 - high corrosion stress                       |
| LABS (PWIS) conformity         | VDMA24364-B2-L                                  |
| Media resistance               | Dust<br>Chips<br>Oils<br>Grease<br>Petrol       |
| Degree of protection           | IP54  |
| Ambient temperature            | -10 °C...80 °C                                  |
| Product weight                 | 85 g  |
| Type of mounting               | Push-on<br>Via threaded pin                     |
| Pneumatic connection           | G1/8  |
| Note on materials              | RoHS-compliant                                  |
| Material adapter components    | PA-reinforced                                   |
| Material seals                 | NBR   |
| Material bellows               | NBR   |
| Material threaded pin          | High-alloy stainless steel                      |