


Shock absorber DYSC-16-18-Y1F

Part number: 553593

FESTO



Data sheet

Feature	Value
Size	16
Stroke	18 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Max. impact speed	3 m/s
Reset time at room temperature	0.3 s
Reset time at min. ambient temperature	1 s
Mode of operation	Single-acting Pushing
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Cushioning length	18 mm
Max. stop force	2000 N
Max. energy consumption per stroke	25 J
Max. energy consumption per hour	50000 J
Max. residual energy	0.16 J
Reset force	6 N
Min. insertion force	60 N
Product weight	210 g
Load range	70 kg
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Galvanised steel
Material piston rod	High-alloy steel