

Plastic tubing PAN-16X2-SW-100

Part number: 553905

FESTO



Data sheet

Feature	Value
Outside diameter	16 mm
Flow-relevant bending radius	94 mm
Inside diameter	12 mm
Min. bending radius	67 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight according to length	0.092 kg/m
Pneumatic connection	For push-in connector O.D. 16 mm
Colour	Black
Shore hardness	D 55 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A