

plastic tubing PUN-10X1,5-SW-300

Part number: 553940

FESTO

Standard O.D tubing, for QS plug connectors, CN and CK polyurethane fittings (not approved for use in the food industry).



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	54 mm
Inside diameter	7 mm
Min. bending radius	28 mm
Instructions for use	TPE-U Ester based The plastic tubing can only be installed in contact with cables if the sheathing is free from phosphoric acid esters. Otherwise the plastic tubing can get damaged.
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.7 MPa
Operating pressure complete temperature range	-0.95 ... 7 bar
Operating pressure for entire temperature range	-13.775 ... 101.5 psi
Temperature-dependent operating pressure	-0.095 ... 1 MPa
Temperature dependent operating pressure	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
Authorisation	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.0489 kg/m
Pneumatic connection	For push-in connector outside diameter 10 mm
Colour	Black
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)