


drive shaft EAMB-18-9-8X16-10X12

Part number: 558035

FESTO

for adapting drives with hollow shaft



Data sheet

Feature	Value
Holder diameter 1	8 mm
Holder diameter 2	10 mm
Size	70
Nominal length	16 mm
Assembly position	Any
Max. speed	8,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.838 kgmm ²
Transferable torque	12 Nm
Product weight	29 g
Materials note	Conforms to RoHS