

Push-in L-fitting NPQM-LK-G18-Q8-P10

Part number: 558820

FESTO



Data sheet

| Feature | Value |
|-----------------------------------------------|---------------------------------------------------------------------|
| Size | Standard |
| Nominal size | 6 mm |
| Type of seal on screwed plug | Sealing ring |
| Design | L-shape Push-pull principle |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...70 °C |
| Nominal torque | 6 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 25.7 g |
| Type of mounting | Internal hexagon, size 4 mm |
| Pneumatic connection, port 1 | Male thread G1/8 |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm |
| Note on materials | RoHS-compliant |
| Material housing | Brass, nickel-plated |
| Material hollow bolt | Nickel-plated brass |
| Material tubing seal | NBR |