


axial kit EAMM-A-S38-42A

Part number: 560685
☆ Core product range

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	3.5 Nm
Product weight	410 g
Interface code, actuator	S38
Interface code, motor in	42A
Materials note	Conforms to RoHS