

End plate VMPAL-EPL-SD25

Part number: 560938

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width | 43 mm |
| Length | 107.3 mm |
| Max. number of valve positions | 24 |
| Valve terminal structure | Valve sizes can be mixed |
| Max. number of valve coils | 24 |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Pilot pressure | 0.3 MPa...0.8 MPa 3 bar...8 bar |
| Nominal operating voltage DC | 24 V |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP67 |
| Note on degree of protection | In assembled state with accessories VMPAL-KM |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 190 g |
| Electrical connection 1, function | Multi-pin plug |
| Electrical connection 1, connection type | Plugs |
| Electrical connection 1, connector system | Sub-D |
| Electrical connection 1, number of connections/cores | 25 |
| Note on materials | RoHS-compliant |
| Material end plate | Die-cast aluminium PA-reinforced |