

Plate VMPAL-EG-QS10

Part number: 560957

FESTO



Data sheet

| Feature | Value |
|-----------------------------------|--|
| Width | 20.5 mm |
| Length | 107.3 mm |
| Integrated function | Ducted exhaust air |
| Valve terminal structure | Valve sizes can be mixed |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Pressure regulation range | 0.5 bar...5 bar |
| Inlet pressure 1 | 0.5 bar...10 bar |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 30 g |
| Pneumatic connection 3/5 combined | For tubing O.D. 10 mm |
| Note on materials | RoHS-compliant |
| Material plate | PA |