


axial kit EAMM-A-P10-38A-55A

Part number: 562659

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	12.5 Nm
Product weight	130 g
Interface code, actuator	P10-38A
Interface code, motor in	55A
Interface code, coupling housing	38A
Materials note	Conforms to RoHS