

Blanking plug QBC-1/4H-U

Part number: 564786

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Mounting position | optional |
| Design | Blanking plug Push-pull principle |
| Size of pack | 10 |
| Operating pressure complete temperature range | 0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | 0 °C...60 °C 32 °F...140 °F |
| Product weight | 28,1 oz |
| Pneumatic connection, port 1 | Push-in sleeve diameter 1/4" " |
| Note on materials | RoHS-compliant |