

Push-in T-connector QBT-1/4T-5/32-U

Part number: 564805

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	0,126 in
Mounting position	optional
Design	T-shape Push-pull principle
Size of pack	10
Operating pressure complete temperature range	0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C 32 °F...140 °F
Product weight	232 oz
Pneumatic connection, port 1	For tubing O.D. 1/4" "
Pneumatic connection, port 2	For tubing outside diameter of 5/32" "
Colour of release ring	grey
Note on materials	RoHS-compliant
Material housing	PBT
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel