

# manifold rail

## VABM-B6-E-G12-16

Part number: 564835

FESTO

For VUVB solenoid valves.



### Data sheet

Feature	Value
Grid dimension	21 mm
Max. number of valve positions	16
Corrosion resistance classification CRC	2
Max. tightening torque, H-rail mounting	1.5 Nm
Max. tightening torque, valve mounting	2 Nm
Max. tightening torque, wall mounting	5 Nm
Product weight	2,100 g
Auxiliary pilot air port 12/14	G1/8
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 3	G1/2
Materials note	Free of copper and PTFE Conforms to RoHS
Material information, manifold strip	Wrought Aluminium alloy