


Motor cable NEBM-S1G9-E-5-N-S1G9

Part number: 565370

FESTO

for connecting motor and end-position controller CMFL.



Data sheet

Feature	Value
Cable attribute	Suitable for chain link trunking
Degree of contamination	3
Protection class	in assembled condition IP65
Ambient temperature with flexible cable installation	-40 ... 90 °C
Ambient temperature	-50 ... 90 °C
Min. cable bending radius	65 mm
Cable structure	2x0,5 mm ² +3x(2x0,14 mm ²)D +1x0,14mm ² Shielded
Cable length	5 m
Materials note	Conforms to RoHS
Materials information, cable sheaths	TPE-U(PUR)