

Plastic tubing PEN-U

Part number: 567448

FESTO



Data sheet

| Feature | Value |
|--|--|
| Outside diameter inch | 5/8 |
| Tubing characteristics | Suitable for energy chains in applications with higher cycle rates |
| Tubing test conditions | Suitability for energy chains: > 5 million cycles according to FN 942021 |
| Temperature-dependent operating pressure | -14,4 psi...58 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -22 °F...140 °F |
| Pneumatic connection | For push-in connector outside diameter of 5/8" " |
| Colour | Blue Brown Yellow Green Natural Red Black Silver White |
| Note on materials | RoHS-compliant |
| Material tubing | PE |