

Plastic tubing PLN-5/8-SW-150-CB

Part number: 569911

FESTO



Data sheet

Feature	Value
Outside diameter inch	5/8
Flow-relevant bending radius	0,311 Feet
Min. bending radius	0,197 Feet
Temperature-dependent operating pressure	-14,4 psi...203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	-22 °F...176 °F
Product weight according to length	oz/ft
Pneumatic connection	For push-in connector outside diameter of 5/8" "
Colour	Black
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material tubing	PE