

Plastic tubing PAN-M-4X0,75-NT

Part number: 572083

FESTO



Data sheet

| Feature | Value |
|--|---|
| Outside diameter | 4 mm |
| Bending radius relevant for flow rate | 15 mm |
| Inside diameter | 2.5 mm |
| Min. bending radius | 10 mm |
| Temperature dependent operating pressure | -0.95 ... 42 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7::-] |
| Ambient temperature | -60 ... 100 °C |
| Product weight according to length | 0.008 kg/m |
| Colour | neutral |
| Shore hardness | D 65 +/-3 |
| Materials note | Free of copper and PTFE Conforms to RoHS |
| Materials information for tubing | Polyamide 12 |